FD3-PA072J2AU3520



FDH 3000 Fiber Distribution Hub in a Pedestal, 72F, SC/APC,(2) 32-splitter module, stranded pigtails, 72 splice cap., 12F spliced feeder

- Metal cabinet and can be placed in the ground without pouring a concrete pad or installing a hand hole
- Typically deployed for neighborhoods of 144 homes or higher
- Features full size trays for splicing incoming feeder and outgoing distribution cables and the option of adding hardened drop connections
- Modeled after the FDH 3000 fiber distribution hubs

Product Classification

Regional Availability North America

Product Type Hub in a pedestal

Product Series FDH 3000

General Specifications

Access Front

Cable TypePigtails - Stranded

Color Putty white

Distribution Ports, quantity 72

Fibers per Feeder Cable, quantity 12

Interface, Input SC

Interface Feature, Input APC

Mounting Pedestal

Splice Tray Included, quantity 3

Splice Tray Type Included 24-way, heat shrink

Splicing Capacity, maximum 72
Splitter Slots, quantity 6

Dimensions

Enclosure Size Small

Material Specifications

Finish Powder coated



FD3-PA072J2AU3520

Material Type Molded plastic

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Included Cable fixation kit (5)

Packaging quantity 1

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

