

PPB3-14MKIINO

ProPatch® Professional Normals Out Patchbays, 2 x 48 bantam, QCP II, 14 in chassis

Product Classification

Regional Availability	EMEA Latin America North America
Product Type	Audio patch panel
Product Brand	Pro Patch®
Product Series	ProPatch

General Specifications

Application	For use with Bantam audio patch cords
Growth Configuration	Fully loaded
Interface, front	Bantam jack
Interface, rear	QCP Mark II block
Mounting	Rack, horizontally oriented
Rack Type	EIA 19 in
Rack Units	2
Termination Type	IDC
Total Ports, quantity	96
Wiring	Normals out

Dimensions

Height	88.9 mm 3.5 in
Width	482.6 mm 19 in
Depth	35.6 mm 1.402 in

Material Specifications

Finish	Powder coated
Material Type	Steel

Mechanical Specifications

Plug Insertion Force, maximum	31 N 6.969 lbf
Plug Insertion Life, minimum	20000 times
Plug Retention Force, minimum	9 N 2.023 lbf

PPB3-14MKIINO

Environmental Specifications

Operating Temperature	-40 °C to +65 °C (-40 °F to +149 °F)
Storage Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Relative Humidity	Up to 95%, non-condensing
Environmental Standard	MIL-STD-202
Flammability Rating	UL 94 V-0

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted

