

PPE1232-CJMT-BK

ProPatch® Economical Midsize Straight-Through Jacks, 1 RU, CJMT terminated, 2 x 32, black

Product Classification

Regional Availability	EMEA Latin America North America
Product Type	Video patch panel
Product Brand	Pro Patch®
Product Series	ProPatch

General Specifications

Application	For use with WECO HD midsize video patch cords
Color	Black
Growth Configuration	Fully loaded
Interface, front	CJMT jack
Interface, rear	BNC female adapter
Mounting	Rack, horizontally oriented
Rack Type	EIA 19 in
Rack Units	1
Total Ports, quantity	64
Wiring	Straight through

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in

Electrical Specifications

Characteristic Impedance	75 ohm
---------------------------------	--------

Material Specifications

Finish	Powder coated
Material Type	Steel

Mechanical Specifications

Plug Insertion Force, maximum	7 N 1.574 lbf
Plug Insertion Life, minimum	10000 times

PPE1232-CJMT-BK

Plug Retention Force, minimum 2 N | 0.45 lbf

Environmental Specifications

Operating Temperature -40 °C to +65 °C (-40 °F to +149 °F)
Storage Temperature -55 °C to +85 °C (-67 °F to +185 °F)
Relative Humidity Up to 95%, non-condensing
Environmental Standard MIL-STD-202
Flammability Rating UL 94 V-0

Packaging and Weights

Included Designation strips

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

