



OCM6 Fiber Optic Splitter Module, Planar, one 1x8 Splitter, singlemode, SC /APC, symmetrical split ratio, butt style, 3 m pigtailed

Product Classification

Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Splitter module
Product Series	OCM6

General Specifications

Device Type	Standard VAM
Functionality	Splitting
Technology Type	Planar lightwave circuit (PLC)
Application	For use with BUDI wall boxes
Circuits, quantity	1
Distribution Type	1 x 8 splitter
Interface, Input	SC
Interface Feature, Input	APC
Interface, Output	SC
Interface Feature, Output	APC
Split Ratio	Symmetrical
Splitter, quantity	1

Dimensions

Height	130 mm 5.118 in
Width	49.8 mm 1.961 in
Depth	16.5 mm 0.65 in
Pigtail Length, Input	3 m 9.843 ft

760235614 | OCM6-SP118S2-30DB1

Pigtail Length, Output 3 m | 9.843 ft
Pigtail Diameter 1.8 mm | 0.071 in

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance