

760236112 | DM24-24LC-LS-ULL



G2 ULL Multimode OM4 MPO-24 Distribution Module, 24LC to 1X24f MPO unpinned, internal shutters

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber module
Product Brand	SYSTIMAX ULL
Product Series	G2

General Specifications

Functionality	Breakout
Color, front	Aqua
Color, rear	Gray
Interface, front	LC/UPC
Interface, rear	MPO
Interface Feature, rear	Key up/up MPO Non-Pinned
Polarity	Method B Enhanced (ULL)
Shuttered	Yes
Total Fibers, quantity	24

Dimensions

Height	26.42 mm 1.04 in
Width	96.52 mm 3.8 in
Depth	117.35 mm 4.62 in

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM4 OM4, LazrSPEED® 550
Insertion Loss, maximum	0.35 dB

760236112 | DM24-24LC-LS-ULL

Environmental Specifications

Qualification Standards IEC 61753-1 | TIA-568.3-D

Safety Standard CE | CSA | UL

Packaging and Weights

Packaging quantity 1

Weight, net 0.113 kg | 0.249 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

