

760238085 | DM12iP-24LC-SM-ULL

G2 ULL Singlemode MPO-12 Distribution Module, 2x12F MPO unpinned to 24F LC Blue, Method B Enhanced, iPatch Ready



Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber module
Product Brand	SYSTIMAX ULL TeraSPEED®

General Specifications

Functionality	Breakout
Adapters, quantity, front	24
Adapters, quantity, rear	2
Color, front	Blue
Color, rear	Blue
Data Module Type	Standard
Intelligence Type	iPatch® ready
Interface, front	LC/UPC
Interface, rear	MPO
Interface Feature, rear	Key up MPO Non-Pinned
Polarity	Method B Enhanced (ULL)
Shuttered	Yes
Total Fibers, quantity	24
Total Ports, quantity, front	24

Dimensions

Height	24.64 mm 0.97 in
Width	94 mm 3.701 in

760238085 | DM12iP-24LC-SM-ULL

Depth 113.28 mm | 4.46 in

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A2

Insertion Loss, maximum 0.6 dB

Environmental Specifications

Qualification Standards TIA/EIA-568-C.3

Safety Standard cUL US 1863

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

