



OCM6 Fiber Optic Splitter Module, Planar, five 1x4 Splitters, singlemode, LC/APC, symmetrical split ratio, butt style, 1.6 m pigtailed

Product Classification

Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Splitter module
Product Series	OCM6

General Specifications

Device Type	Standard VAM
Functionality	Splitting
Technology Type	Planar lightwave circuit (PLC)
Application	For use with BUDI wall boxes
Circuits, quantity	5
Distribution Type	1 x 4 splitter
Interface, Input	LC
Interface Feature, Input	APC
Interface, Output	LC
Interface Feature, Output	APC
Split Ratio	Symmetrical
Splitter, quantity	5

Dimensions

Height	130 mm 5.118 in
Width	49.8 mm 1.961 in
Depth	16.5 mm 0.65 in
Pigtail Length, Input	1.6 m 5.249 ft

760238447 | OCM6-SP514L2-16DB1

Pigtail Length, Output 1.6 m | 5.249 ft

Pigtail Diameter 1.8 mm | 0.071 in

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

REACH-SVHC

Classification

Compliant as per SVHC revision on www.commscope.com/ProductCompliance