

# 760242454 | EPX-1U-MOD-OPEN-ANG (AGL-1U-ANG-SL)

---



EPX 1U angled sliding panel, accepts (4) G2 modules or adapter packs providing up to 48 duplex LC or 32 MPO ports

## Product Classification

<b>Regional Availability</b>	EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel
<b>Product Series</b>	EPX

## General Specifications

<b>Application</b>	Accepts four G2 modular cassettes
<b>Color</b>	Black
<b>Intelligence Type</b>	Not iPatch® ready
<b>Interface, front</b>	Unloaded
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	1
<b>Shelf Movement</b>	Sliding

## Dimensions

<b>Height</b>	43.6 mm   1.717 in
<b>Width</b>	483 mm   19.016 in
<b>Depth</b>	278 mm   10.945 in

## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel

## Environmental Specifications

<b>Safety Standard</b>	UL
------------------------	----

## Packaging and Weights

# 760242454 | EPX-1U-MOD-OPEN-ANG (AGL-1U-ANG-SL)

---

**Packaging quantity** 1  
**Weight, net** 1.742 kg | 3.84 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

