

7L5827-000 | OCMF-CMD471L1

OCMF LGX Fiber Optic Module, CWDM, Mux, LC/UPC, 8 channels, starting wavelength 1470 nm

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	WDM module
Product Series	LGX

General Specifications

Device Type	Standard VAM
Functionality	Multiplexing
Application	For use with OMX frames
Circuits, quantity	1
Distribution Type	8-channel CWDM
Interface, Input	LC/UPC
Interface, Output	LC/UPC
Multiplexers, quantity	1
Port Type, optional	1310 nm port Upgrade port

Dimensions

Width	16 mm 0.63 in
--------------	-----------------

Optical Specifications

Starting Wavelength	1471 nm
----------------------------	---------

Packaging and Weights

Packaging quantity	1
Packaging Type	Box Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance

7L5827-000 | OCMF-CMD471L1

ROHS

Compliant

UK-ROHS

Compliant/Exempted

