CC6925-000 | OCM5-SP11W00S2-14DASIA-U



OCM5 Fiber Optic Splitter Module, Planar, one 1x32 Splitter, singlemode, SC/APC, symmetrical split ratio, 1.4 m pigtails

Product Classification

Regional Availability EMEA

PortfolioCommScope®Product TypeSplitter module

Product Series OCM5

General Specifications

Device Type Standard VAM

Functionality Splitting

Technology Type Planar lightwave circuit (PLC)

Access Front

Application For use with FIST cabinets

Circuits, quantity 1

Distribution Type 1 x 32 splitter

 Interface, Input
 SC

 Interface Feature, Input
 APC

 Interface, Output
 SC

 Interface Feature, Output
 APC

Split Ratio Symmetrical

Splitter, quantity

Dimensions

 Height
 154 mm | 6.063 in

 Width
 16 mm | 0.63 in

 Depth
 142 mm | 5.591 in

Page 1 of 2



CC6925-000 | OCM5-SP11W00S2-14DASIA-U

Pigtail Length, Input $1.4 \, \mathrm{m}$ | $4.593 \, \mathrm{ft}$ Pigtail Length, Output $1.4 \, \mathrm{m}$ | $4.593 \, \mathrm{ft}$

Packaging and Weights

Packaging quantity

Packaging Type Box | Carton

