356755-000 | FOSC100-BM-48



FOSC® 100C Fiber Optic Splice Closure, Heat Shrink Cable sealing, 48 splices

Product Classification

Regional Availability Latin America

Product Type Single-ended, round fiber closure

Product Brand FOSC®
Product Series FOSC 100

General Specifications

Cable Entry Drop Port StyleRoundCable Entry Main Port StyleOval

Cable Ports Quantity, total1 oval port (2 cables) + 4 round ports

Cable Sealing Type Heat shrink

Closure Sealing Type Dome-to-base clamp with O-ring

Closure Style Single-ended

Color Black

Mounting Pole | Strand | Wall

Network Area Type Feeder

Splice Tray Included, quantity 2

Splice Tray Type Included 24-way, heat shrink

Splicing Type, Supported Single fusion

Dimensions

 Length
 540 mm | 21.26 in

 Diameter
 150 mm | 5.906 in

 Main Cable Diameter, maximum
 25 mm | 0.984 in

Ordering Tree



356755-000 | FOSC100-BM-48

FOSC 100 - BM -XX-X-XXX Valve for Flash Test Capacity of Splice Tray Valve Splice Tray for holding up to 24 splices No Valve Splice Tray for holding up to 48 splices Splice Tray for holding up to 72 splices Splice Tray for holding up to 96 splices **Ground Feed-through Lugs** Grounding None **Cable Blocking Components Number of Splice Trays** Blocking O or 1 is standard None

Material Specifications

Material Type Impact-resistant polymer

Environmental Specifications

Environmental Space Below ground | Buried

Water Resistance Flash test valve at 5 psi (40 kPa)

Packaging and Weights

Packaging quantity 1

Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

