

760034108 | MODG2-6SC-SM-PT-B



G2 Modular Cassette with 6 SC TeraSPEED® Singlemode Pigtails, Type B

OBSOLETE

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTEMAX®
Product Type	Fiber cassette with pigtails
Product Brand	TeraSPEED®

General Specifications

Adapter Color	Blue
Interface, front	SC/UPC
Interface, rear	Stranded pigtail
Total Fibers, quantity	6
Total Ports, quantity, front	6

Dimensions

Height	30.48 mm 1.2 in
Width	91.44 mm 3.6 in
Depth	119.38 mm 4.7 in
Pigtail Length	1.5 m 4.921 ft

Optical Specifications

Fiber Type	G.652.D and G.657.A1, TeraSPEED® OS2
Insertion Loss, typical	0.4 dB
Return Loss, minimum	55 dB

Environmental Specifications

760034108 | MODG2-6SC-SM-PT-B

Safety Standard UL

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

Included Products

760049783 - TeraSPEED® SC Multiport Shuttered Adapter, Blue, Single Pack
SFA-SC06-BL-SHUTTERED