



Rack, 2-Post, (58U), 6 in (152 mm) Channel x 9 ft (2743 mm) H x 19 in (482.6 mm) W, steel, 3/8 square punch, black

OBSOLETE

This product was discontinued on: November 30, 2018

Replaced By:

760090142
RK6-52S

Equipment Rack, 2-Post, 6 in (152 mm) Channel x 8 ft (2438 mm) H - 19 in (482.6 mm) Steel (52U) 3/8 Sq Punch, Black

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	2 post rack

General Specifications

Color	Black
Rack Type	EIA 19 in
Rack Units	58
Rail Mounting Hole	3/8 in

Dimensions

Height	2,743.2 mm 108 in
Channel Width	152.4 mm 6 in
Width	515.62 mm 20.3 in
Depth	457.2 mm 18 in
Dimensional Standards	EIA-310-D

Material Specifications

Finish	Powder-coated, textured
Material Type	Steel

760139121 | RK6-58S

Mechanical Specifications

Load Rating 453.592 kg | 1000 lb

Packaging and Weights

Included Forty M6 cage nuts | Four M6 x 12 mm mounting screws | Instruction sheet | Twelve 3/8 in split lock washers | Twelve 3/8-16 UNC x 1 in hex head bolts | Twelve 3/8-16 hex nuts | Two extruded base angles | Two extruded top angles | Two vertical rack rails

Packaging quantity 1

Packaging Type Flat packed

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system