

760245496 | G2-SP-12SC



G2 Splice Cassette, 12SC , no pigtails

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber cassette
Product Series	G2

General Specifications

Color, front	Aqua Blue Green
Interface, front	SC/UPC
Interface, rear	No pigtail
Shuttered	No
Total Fibers, quantity	12

Dimensions

Height	26.416 mm 1.04 in
Width	96.52 mm 3.8 in
Depth	165.354 mm 6.51 in

Material Specifications

Alignment Sleeve Material	Zirconia
----------------------------------	----------

Environmental Specifications

Qualification Standards	IEC 61753-1 TIA-568.3-D
Safety Standard	UL

Packaging and Weights

Included	Colored faceplates SMOUV holder SMOUV splice protection
Packaging quantity	1

Weight, net

0.101 kg | 0.222 lb

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

