

CX0497-000 | FIST-GPS2-M-APL1-6

FIST-GPS2 Fiber Termination/Splice Panel, LC/UPC, 3RU, with 6 trays, ETSI width, gray

Product Classification

Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Brand	FIST®
Product Series	FIST-GPS2

General Specifications

Functionality	Patching Splicing
Application	Used in FIST-GR3-style frames only
Color	Gray
Color, front	Gray
Interface, front	LC/UPC
Rack Type	ETSI 600 mm
Rack Units	3
Shelf Movement	Sliding

Dimensions

Height	133.35 mm 5.25 in
Width	531 mm 20.906 in

Material Specifications

Finish	Powder coated
Material Type	Galvanized steel

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Environmental Specifications

Operating Temperature	-5 °C to +45 °C (+23 °F to +113 °F)
Storage Temperature	-30 °C to +60 °C (-22 °F to +140 °F)

CX0497-000 | FIST-GPS2-M-APL1-6

Relative Humidity Up to 93%, non-condensing

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

