EG9027-000 | OCFPS1U-DDQ1204L2-U23-SUB





Product Classification

Regional AvailabilityNorth AmericaPortfolioCommScope®

Product Type DWDM patch panel

Product Series OCFPS

General Specifications

Device TypePatch panelFunctionalityDemultiplexing

Technology Type Thin film filter (TFF)

Circuits, quantity 1

Distribution Type 40-channel DWDM

Interface, front LC/APC

Multiplexers, quantity

Port Type, optional Upgrade port

Rack Units 1

Dimensions

 Height
 43.5 mm | 1.713 in


 Width
 440 mm | 17.323 in

 Depth
 210 mm | 8.268 in

Ordering Tree



EG9027-000 | OCFPS1U-DDQ1204L2-U23-SUB



Optical Specifications

Channel Spacing 100 GHz **Starting Wavelength** 1,561.42 nm

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

