

362409-000 | TRAC-AA-BOLT-1IN1OUT-KIT

TRAC Copper Closure, unpressurized, gel sealed, 17 inch sheath opening, 25 inch long



- Toolless, extendable and re-enterable closure for freebreathing aerial applications
- Consists of three main components: a central body and two end pieces and self support bond system
- Unique convoluted design provides both mechanical and environmental protection
- Recommended for use on polyethylene insulated cable jackets for straight and branch configurations

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

| | |
|------------------------------|-------------------------------|
| Regional Availability | Latin America North America |
| Product Type | Gel sealed closure |
| Product Series | TRAC |

General Specifications

| | |
|-----------------------------------|----------------------------------|
| Application | For use with Polyethylene cables |
| Cable Capacity, maximum | 1 |
| Cable Sealing Type | Gel filled |
| Closure Style | In-line |
| Color | Black |
| Mounting | Strand |
| Splicing Capacity, maximum | 200 |

Dimensions

| | |
|--|--------------------|
| Length | 635 mm 25 in |
| Single Cable Diameter, maximum | 31.75 mm 1.25 in |
| Single Cable Diameter, minimum | 10.16 mm 0.4 in |
| Splice Bundle Diameter, maximum | 50.8 mm 2 in |
| Sheath Opening, nominal | 431.8 mm 17 in |

Environmental Specifications

Environmental Space Aerial

Packaging and Weights

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

| Agency | Classification |
|------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

