

# 760236504 | PNL-CS-24LCW



TeraSPEED® Splicing cassette, 24LC , No Pigtails

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber cassette

## General Specifications

<b>Adapter Color</b>	Blue
<b>Interface, front</b>	LC/UPC
<b>Interface, rear</b>	No pigtail
<b>Total Fibers, quantity</b>	0
<b>Total Ports, quantity, front</b>	12

## Dimensions

<b>Height</b>	28.956 mm   1.14 in
<b>Width</b>	104.648 mm   4.12 in
<b>Depth</b>	165.354 mm   6.51 in

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
-------------------	------------

## Environmental Specifications

<b>Safety Standard</b>	UL
------------------------	----

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

# 760236504 | PNL-CS-24LCW

---

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

ROHS

Compliant

UK-ROHS

Compliant

