

760245734 | CHD-SP-12LC-LSR-AS-ULL

CHD ULL Multimode OM4 Splice Cassette, 12LC, with dust plugs and ribbon pigtails

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber cassette with ribbon pigtail
Product Brand	SYSTIMAX ULL
Product Series	CHD

General Specifications

Color, front	Aqua
Interface, front	LC/UPC
Interface, rear	Ribbon pigtail
Polarity	Method A Pairs, straight
Shuttered	No
Total Fibers, quantity	12

Dimensions

Height	12.446 mm 0.49 in
Width	83.82 mm 3.3 in
Depth	184.658 mm 7.27 in

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM4, LazrSPEED® 550
Insertion Loss, maximum	0.15 dB

Environmental Specifications

Qualification Standards	IEC 61753-1 TIA-568.3-D
Safety Standard	CE CSA UL

Packaging and Weights

Included	Mass Fusion Splice Protection Sleeves
-----------------	---------------------------------------

Packaging quantity 1
Weight, net 0.095 kg | 0.21 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

- FST-ACC006 – Fiber Optic Protective Splice Sleeve, 12f mass fusion, 5 pack

FST-ACC006



Fiber Optic Protective Splice Sleeve, 12f mass fusion, 5 pack

Product Classification

Regional Availability North America
Product Type Fiber protection sleeve

General Specifications

Splicing Type Heat shrink, mass fusion

Environmental Specifications

Storage Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

Packaging quantity 5

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

