

7712941-00



Rack, 4-Post, 19" 24 HU 800x800 open frame

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Product Type 4 post rack

General Specifications

Color Gray
Mounting M6 Cage nut rail mounting
Note Static load rating is 1000 kg
Rack Type EIA 19 in

Dimensions

Height 1200 mm | 47.244 in
Height, guide rails 1,066.8 mm | 42 in
Width 800 mm | 31.496 in
Depth 800 mm | 31.496 in

Electrical Specifications

Electrical Safety Standard UL | cUL
Voltage Range On-site configuration dependant

Material Specifications

Material Type Galvanized sheet metal | Powder-coated, textured

Packaging and Weights

Height, packed 1400 mm | 55.118 in

7712941-00

Width, packed	960 mm 37.795 in
Depth, packed	1222 mm 48.11 in
Included	Cables ducts (2) Cage nuts M6 (30) Grounding cables (10) Grounding rail (1) Guide rails (16) Raised head screws M6 (30)
Packaging quantity	1
Weight, gross	105 kg 231.485 lb
Weight, net	42 kg 92.594 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015



Classification

Designed, manufactured and/or distributed under this quality management system