

TTRC Copper Closure, unpressurized, gel sealed, 510 mm sheath opening, for up to 300 pair splices



- Watertight, toolless, torchless and re-usable closure for aerial applications
- Seals unpressurised inline splices in new construction and network maintenance applications up to 600 pairs
- Sealing on both the closure body and a multiple of cables is performed by compressing the gel material between two plastic flanges
- Gel compression is activated by a built-in tensioning mechanism

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Regional Availability	EMEA
Product Type	Gel sealed closure
Product Series	TTRC

General Specifications

Application	For use with Polyethylene cables
Cable Capacity, maximum	2
Cable Sealing Type	Gel filled
Closure Style	In-line
Color	Black
Mounting	Strand
Splicing Capacity, maximum	600

Dimensions

Single Cable Diameter, maximum	26 mm 1.024 in
Single Cable Diameter, minimum	10 mm 0.394 in
Splice Bundle Diameter, maximum	126 mm 4.961 in
Sheath Opening, nominal	510 mm 20.079 in

Environmental Specifications

Environmental Space Aerial

Packaging and Weights

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

