



MJC Copper Closure, unpressurized, gel sealed, cap-ended, for up to 50 /100 pair splices

- Watertight splice closure for aerial, underground and direct buried splices in the unpressurized copper telecommunication network
- Flexible branching plug system allowing installation of cables from 5-pair to 100pair
- Reduced inventory as fewer size closures needed to cover a wide range of applications up to 100 pairs

Product Classification

Regional Availability	EMEA
Product Type	Gel sealed closure
Product Series	MJC

General Specifications

Application	For use with Polyethylene cables
Cable Capacity, maximum	4
Cable Sealing Type	Gel filled
Closure Style	Single-ended
Color	Black
Splicing Capacity, maximum	50

Dimensions

Length	185 mm 7.283 in
Single Cable Diameter, maximum	28 mm 1.102 in
Single Cable Diameter, minimum	7 mm 0.276 in
Splice Bundle Diameter, maximum	120 mm 4.724 in

Environmental Specifications

Environmental Space	Aerial Buried
----------------------------	-----------------

Packaging and Weights

Packaging quantity	1
Packaging Type	Bag Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

