

# CK9323-000 | FOSC-RSKG-4



FOSC® Gel Sealing Kit for round splice closure port, sealing 4 cables with diameter between 4 and 7 mm

- Unique gel-based mechanical sealing option used on fiber splice closure ports for blown, standard, mini- and micro-cables
- Allows usage of multiple cable drops in a single closure outlet port, thus significantly increasing existing cable capacity
- Ideal for fiber cables with thin outer jackets that are difficult to seal with standard heat shrinkable sleeves

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Gel sealing kit
<b>Product Brand</b>	FOSC®
<b>Product Series</b>	FOSC 400G

## General Specifications

<b>Application</b>	For use with FOSC-400G Fiber closures
<b>Cable Capacity, maximum</b>	4
<b>Color</b>	Black

## Dimensions

<b>Single Cable Diameter, maximum</b>	7 mm   0.276 in
<b>Single Cable Diameter, minimum</b>	4 mm   0.157 in

## Packaging and Weights

<b>Included</b>	Cable termination brackets   Dummy plugs   Multi-out gel seal
<b>Packaging quantity</b>	1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant

UK-ROHS

Compliant

