

CU5172-000 | FIST-OSKG20



FIST Gel Sealing Kit for oval splice closure port, sealing 1 looped cable with diameter between 16 and 20 mm

- Unique gel-based mechanical sealing option used on fiber splice closure ports for blown, standard, mini- and micro-cables
- Allows usage of multiple cable drops in a single closure outlet port, thus significantly increasing existing cable capacity
- Ideal for fiber cables with thin outer jackets that are difficult to seal with standard heat shrinkable sleeves

Product Classification

| | |
|------------------------------|-----------------|
| Regional Availability | EMEA |
| Product Type | Gel sealing kit |
| Product Series | FIST-GC02 |

General Specifications

| | |
|--------------------------------|---------------------------------------|
| Application | For use with FIST-GC02 Fiber closures |
| Cable Capacity, maximum | 1 |
| Color | Black |

Dimensions

| | |
|---------------------------------------|------------------|
| Single Cable Diameter, maximum | 20 mm 0.787 in |
| Single Cable Diameter, minimum | 16 mm 0.63 in |

Packaging and Weights

| | |
|---------------------------|---|
| Included | Cable termination brackets Dummy plugs Multi-out gel seal |
| Packaging quantity | 1 |

Regulatory Compliance/Certifications

| Agency | Classification |
|------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |



