

# FL2-72TS140

---



FL2000 Fiber Termination/Splice Panel, unloaded, 72 Ports, 8RU, 19 in, putty white

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch/splice panel
<b>Product Series</b>	FL2000

## General Specifications

<b>Functionality</b>	Patching   Splicing
<b>Cable Exit Location</b>	Rear, left side   Rear, right side
<b>Color</b>	Putty white
<b>Growth Configuration</b>	Unloaded
<b>Interface, front</b>	Unloaded
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	8
<b>Shelf Movement</b>	Hinged
<b>Splicing Capacity, maximum</b>	72
<b>Total Ports, quantity</b>	72

## Dimensions

<b>Height</b>	355.6 mm   14 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	256.54 mm   10.1 in

## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel

# FL2-72TS140

---

## Environmental Specifications

**Operating Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Storage Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

## Packaging and Weights

**Included** Mounting hardware

**Packaging quantity** 1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant/Exempted

