FL2-C470048PW-4C00



FL2000 Fiber Termination/Splice Panel, pre-terminated with pigtails, 48 SC/UPC, singlemode, 5RU, 19 in, putty white

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch/splice panel

Product Series FL2000

General Specifications

Functionality Patching | Splicing

Adapter Packs Included, quantity 8

 Cable Exit Location
 Rear, left side | Rear, right side

Color Putty white

Growth Configuration Fully loaded

Interface, front SC/UPC

Rack Type EIA 19 in

Rack Units 5

Shelf Movement Hinged

Splicing Capacity, maximum 48

Total Ports, quantity 48

Dimensions

 Height
 222.25 mm | 8.75 in


 Width
 482.6 mm | 19 in

 Depth
 256.54 mm | 10.1 in

Ordering Tree



FL2-C470048PW-4C00



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Storage Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

COMMSCOPE®

FL2-C470048PW-4C00

Regulatory Compliance/Certifications

Classification

Agency CHINA-ROHS Below maximum concentration value ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system **REACH-SVHC** Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant **UK-ROHS** Compliant

