FL2-R2N0024A0-0C00



FL2000 Fiber Termination Panel, 24 SC/UPC, singlemode, 2RU, 19 in, putty white

Product Classification

Regional Availability Latin America | North America

 Portfolio
 CommScope®

 Product Type
 Fiber patch panel

Product Series FL2000

General Specifications

Functionality Patching

Adapter Packs Included, quantity 4

Color Putty white

Growth ConfigurationFully loadedInterface, frontSC/UPCRack TypeEIA 19 in

Rack Units 2

Shelf Movement Hinged

Splicing Capacity, maximum 0

Total Ports, quantity 24

Dimensions

 Height
 88.9 mm | 3.5 in


 Width
 482.6 mm | 19 in

 Depth
 256.54 mm | 10.1 in

Ordering Tree



FL2-R2N0024A0-0C00



Material Specifications

Finish Powder coated

Material Type Steel

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

COMMSCOPE®

FL2-R2N0024A0-0C00

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

