FL2-R470048A0-0A00



FL2000 Fiber Termination Panel, 48 SC/UPC, singlemode, 3RU, 19 in, putty white

Product Classification

Regional Availability Latin America | North America

EIA 19 in

PortfolioCommScope®Product TypeFiber patch panel

Product Series FL2000

General Specifications

Functionality Patching

Adapter Packs Included, quantity 8

ColorPutty whiteGrowth ConfigurationFully loadedInterface, frontSC/UPC

Rack Units 3

Shelf Movement Hinged

Splicing Capacity, maximum 0

Total Ports, quantity 48

Dimensions

Rack Type

 Height
 133.35 mm | 5.25 in


 Width
 482.6 mm | 19 in

 Depth
 257 mm | 10.118 in

Ordering Tree



FL2-R470048A0-0A00



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to} + 158 \,^{\circ}\text{F})$

Storage Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications



FL2-R470048A0-0A00

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

