FL2-SE80AA005-AD00



FL2000 Fiber Termination Panel, LC/UPC, singlemode, 5RU, 19 in, putty white, pre-terminated with IFC cable, 5 meters, Stub tail at far end

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch panel, with IFC cable

Product Series FL2000

General Specifications

Functionality Patching

Adapter Packs Included, quantity 12

Cable Exit Location Downward

IFC Cable Stub Type

Color Putty white

Growth Configuration Fully loaded

Interface, front LC/UPC

Interface, rear Stub tail

FIA 19 in **Rack Type**

Rack Units 5

Shelf Movement Hinged

Splicing Capacity, maximum 0

Total Ports, quantity 144

Dimensions

Height 222.25 mm | 8.75 in Width

Depth 256.54 mm | 10.1 in


Cable Length 5 m | 16.404 ft

COMMSCOPE®

482.6 mm | 19 in

FL2-SE80AA005-AD00

Ordering Tree



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Storage Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights



FL2-SE80AA005-AD00

Packaging quantity

1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

