

# FPX-AF-12APROJSP3

---



FPX Fiber Optic Adapter Pack with 3m Stranded Pigtail, Singlemode, 12 fiber, SC/APC adapter, right, green, putty white

## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Fiber adapter pack with pigtails
<b>Product Series</b>	FPX

## General Specifications

<b>Application</b>	For use with FPX panels
<b>Adapter Color</b>	Green
<b>Adapters, quantity, front</b>	12
<b>Body Style</b>	Right orientation   Simplex
<b>Color, front</b>	Putty white
<b>Interface</b>	SC/APC
<b>Pigtail Assembly Type</b>	Color-coded, 900 $\mu\text{m}$   Pigtail bundle
<b>Pigtails Included, quantity</b>	12
<b>Total Fibers, quantity</b>	12
<b>Total Ports, quantity, front</b>	12

## Dimensions

<b>Height</b>	33.02 mm   1.3 in
<b>Width</b>	176.53 mm   6.95 in
<b>Pigtail Length</b>	3 m   9.843 ft

## Ordering Tree

# FPX-AF-12APROJSP3

FPX - AF - X X A P X X X X X X

## Number of Fiber Ports per Bulkhead

12	12 Fibers <sup>1</sup>
24	24 Fibers <sup>2</sup>
00	None

## Pack Orientation

L	Left adapter pack
R	Right adapter pack

## Adapter Style

00	None
Singlemode	
07	SC/APC
0J	SC/APC
08	LC/APC
0Z	LC/APC
Multimode	
A6	LCMM - AQUA <sup>3</sup>
A9	SCMM - AQUA <sup>3</sup>

## Pigtail Length

LEAVE BLANK	Adapters only
3	3 meter pigtails

## Pigtail Type

LEAVE BLANK	Adapters only
R	Ribbon
P	Stranded

## Fiber Type

LEAVE BLANK	Adapters only
S	Singlemode
D	50/125 Multimode (OM3)
Q	50/125 Multimode (OM4)

<sup>1</sup> SC only

<sup>2</sup> LC only

<sup>3</sup> CommScope recommends the use of aqua adapters to identify OM3 and OM4 circuits

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
<b>Fiber Type</b>	OS2
<b>Insertion Loss, maximum</b>	0.35 dB
<b>Return Loss, minimum</b>	65 dB

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
<b>Storage Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)

## Packaging and Weights

<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Bag   Carton

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
---------------	-----------------------

# FPX-AF-12APROJSP3

---

CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

