


FPX-AF-24APR08



FPX Fiber Optic Adapter Pack Only, Singlemode, 24 fiber, LC/UPC adapter, right, blue, putty white

Product Classification

| | |
|------------------------------|--------------------|
| Regional Availability | North America |
| Product Type | Fiber adapter pack |
| Product Series | FPX |

General Specifications

| | |
|-------------------------------------|----------------------------|
| Application | For use with FPX panels |
| Adapter Color | Blue |
| Adapters, quantity, front | 12 |
| Body Style | Duplex Right orientation |
| Color, front | Putty white |
| Interface | LC/UPC |
| Total Ports, quantity, front | 24 |

Dimensions

| | |
|---------------|---------------------|
| Height | 33.02 mm 1.3 in |
| Width | 176.53 mm 6.95 in |

Ordering Tree

FPX-AF-24APR08

FPX - AF - X X A P X X X X X X

Number of Fiber Ports per Bulkhead

| | |
|----|------------------------|
| 12 | 12 Fibers ¹ |
| 24 | 24 Fibers ² |
| 00 | None |

Pack Orientation

| | |
|---|--------------------|
| L | Left adapter pack |
| R | Right adapter pack |

Adapter Style

| | |
|------------|--------------------------|
| 00 | None |
| Singlemode | |
| 07 | SC/APC |
| 0J | SC/APC |
| 08 | LC/APC |
| 0Z | LC/APC |
| Multimode | |
| A6 | LCMM - AQUA ³ |
| A9 | SCMM - AQUA ³ |

Pigtail Length

| | |
|-------------|------------------|
| LEAVE BLANK | Adapters only |
| 3 | 3 meter pigtails |

Pigtail Type

| | |
|-------------|---------------|
| LEAVE BLANK | Adapters only |
| R | Ribbon |
| P | Stranded |

Fiber Type

| | |
|-------------|------------------------|
| LEAVE BLANK | Adapters only |
| S | Singlemode |
| D | 50/125 Multimode (OM3) |
| Q | 50/125 Multimode (OM4) |

¹ SC only

² LC only

³ CommScope recommends the use of aqua adapters to identify OM3 and OM4 circuits

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Storage Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

FPX-AF-24APR08

UK-ROHS

Compliant

