

TFP-12APRC8SB3

TFP Fiber Optic Adapter Pack, 12-fiber, 3 m pigtail, Singlemode, SC, duplex, right, blue

Product Classification

Regional Availability	Asia Latin America North America
Portfolio	NETCONNECT®
Product Type	Fiber adapter pack with pigtails
Product Series	TFP

General Specifications

Application	For use with TFP panels
Adapter Color	Aqua
Adapters, quantity, front	6
Body Style	Duplex Left orientation
Color, front	Black
Interface	SC/UPC
Pigtail Assembly Type	Color-coded, 900 µm Pigtail bundle
Pigtails Included, quantity	12
Total Fibers, quantity	12
Total Ports, quantity, front	12

Dimensions

Height	33.53 mm 1.32 in
Width	176.02 mm 6.93 in
Pigtail Length	3 m 9.843 ft

Ordering Tree

TFP-12APRC8SB3

TFP - X X AP X X X X X

Number of Fiber Ports

12	12 fiber ports: 6 LC adapters; 6 SC duplex adapters; 12 ST adapters
24	24 fiber ports: 12 LC adapters

Pack Orientation

L	angle left
R	angle right

Adapter Style

Multimode Connectors	
C3	SC duplex (beige)
C4	SC duplex (aqua)
Q1	LC (beige)
Q2	LC (aqua)
T1	ST®
Singlemode Connectors	
C8	SC UPC duplex (blue)
A2	SC APC duplex (green)
Q5	LC UPC (blue)
T2	ST UPC

Pigtail Length

Leave	Adapters only
Blank	
3	3 meter pigtails

Pigtail Type

Leave	Adapters only
Blank	
B	Singlemode stranded
E	Multimode stranded

Fiber Size

Leave	Adapters only
Blank	
B	OM1 - 62.5/125 Multimode
D	OM3 - 50/125 LOMMF 300m
S	Singlemode

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	OS2
Insertion Loss, maximum	0.2 dB
Return Loss, minimum	57 dB

Environmental Specifications

Operating Temperature	0 °C to +70 °C (+32 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

Packaging and Weights

Packaging quantity	1
Packaging Type	Bag Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value

TFP-12APRC8SB3

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant/Exempted

