

# F1A-QMRNR

## Base Product



FSJ1-50A SureFlex® Jumper with interface types QMA Male Right Angle and N Male Right Angle, variable length

## Product Classification

|                       |                                      |
|-----------------------|--------------------------------------|
| <b>Product Type</b>   | Wireless transmission cable assembly |
| <b>Product Brand</b>  | HELIAX®   SureFlex®                  |
| <b>Product Series</b> | FSJ1-50A                             |

## General Specifications

|   |   |
|---|---|
| <b>Body Style, Connector A</b>            | Right angle   |
| <b>Body Style, Connector B</b>            | Right angle   |
| <b>Interface, Connector A</b>             | QMA Male  |
| <b>Interface, Connector B</b>             | N Male  |
| <b>Orientation</b>                        | 0°  |
| <b>Specification Sheet Revision Level</b> | A   |
| <b>Variable Length</b>                    | For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative |

## Dimensions

|                     |            |
|---------------------|------------|
| <b>Length</b>       | 0 m   0 ft |
| <b>Nominal Size</b> | 1/4 in     |

## VSWR/Return Loss

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|------|------------------|
| 700–3000 MHz   | 1.43 | 15.04            |

## Jumper Assembly Sample Label

# F1A-QMRNR

---



## Environmental Specifications

**Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |