# ACGLFUCN1

#### **Base Product**



Singlemode LC/UPC to Stub, Fiber Pigtail, Simplex 0.6 mm, Low Smoke Zero Halogen

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber pigtail, unjacketed

Product Series ACG

General Specifications

Connector A, quantity

Color, boot A Blue
Color, connector A Blue

Interface, Connector A LC/UPC

Jacket Color Yellow

**Polarity** Method A

Total Fibers, quantity 1

**Transmission Standards** IEC 61755

**Dimensions** 

Cable Assembly Length Range (m) 1 - 61


Cable Assembly Length Range (ft) 2 - 200

**Diameter Over Jacket** 0.6 mm | 0.024 in

Ordering Tree



## ACGLFUCN1



## Mechanical Specifications

Minimum Bend Radius, loaded50 mm | 1.969 inMinimum Bend Radius, unloaded30 mm | 1.181 inTensile Load, long term, maximum3 N | 0.674 lbfTensile Load, short term, maximum6 N | 1.349 lbf

Cable Crush Resistance, maximum5 N/mm | 28.551 lb/inMating Durability, maximum0.2 dB @ 500 cycles

**Optical Specifications** 

**Fiber Mode** Singlemode

**Fiber Type** G.657.A2, TeraSPEED®

Performance Grade IEC Random Mating Grade B

Insertion Loss, maximum, connector A 0.25 dB

Return Loss, minimum, connector A 50 dB

## **Environmental Specifications**

Operating Temperature -20 °C to +60 °C (-4 °F to +140 °F)

Environmental Space Low Smoke Zero Halogen (LSZH)

## Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

\* Footnotes

**Performance Grade** Guarantee to meet IEC 61755-1 Random Mating requirement

COMMSC PE°