## F4WLCLCAK

#### **Base Product**



Singlemode LC/UPC to LC/UPC, InstaPATCH® 360 Ruggedized Fiber Fanout Cable Assembly, 72-Fiber, Low Smoke Zero Halogen (LSZH)

#### **Product Classification**

Regional Availability Europe | Middle East/Africa

Portfolio CommScope®

Product Type Ruggedized fanout

Product Brand SYSTIMAX InstaPATCH® 360

**Ordering Note**For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length

may vary based on cable configuration | Not available in the United States or Canada

### General Specifications

Color, boot ABlueColor, connector ABlueColor, boot BBlueColor, connector BBlue

Construction Type Stranded

Furcation Color Yellow

Interface, Connector A LC/UPC
Interface, Connector B LC/UPC

Jacket Color Yellow

Fibers per Subunit, quantity 12

Total Fibers, quantity 72

#### **Dimensions**


Cable Assembly Length Range (m) 3 - 305

Cable Assembly Length Range (ft) 8 - 999



## F4WLCLCAK

## Ordering Tree



## Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

**Optical Specifications** 

Fiber Mode Singlemode

**Fiber Type** G.652.D | G.657.A1, TeraSPEED®

## **Environmental Specifications**

**Operating Temperature**  $-10 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \text{ (+14 }^{\circ}\text{F to } +140 \,^{\circ}\text{F)}$ 

Environmental Space Indoor | Low Smoke Zero Halogen (LSZH)

### Regulatory Compliance/Certifications

Agency	Classification
ANATEL	Compliant
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

Page 2 of 3



# F4WLCLCAK



#### Included Products

760239615 N-072-MP-8W-F12YL/B2 Fiber indoor cable, TeraSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 72 fibers, 12 fiber subunits, Singlemode G.652.D and G.657.A1, Gel-free, Feet jacket marking, Yellow jacket color, B2ca Flame rating

860637435

LC/UPC Connector, Singlemode, Blue, Short Boot

