

BK2V-STM



WECO Midsize Plug to Midsize Plug, 0.61 m, black

OBSOLETE

Product Classification

Regional Availability	EMEA Latin America North America
Product Type	RF cable assembly

General Specifications

Application	For use with Midsize video panels
Cable Type	RG59, single
Interface, Connector A	Midsize plug
Interface Feature, connector A	Booted
Interface, Connector B	Midsize plug
Interface Feature, connector B	Booted
Jacket Color	Black

Dimensions

Cord Length	0.61 m 2 ft
Compatible Conductor Gauge, stranded	22 AWG

Electrical Specifications

Data Rate, Supported	Uncompressed HDTV signals (1.485 Gbit/s)
Impedance	75 ohm
Safety Voltage Rating	600 V

Material Specifications

BK2V-STM

Conductor Material	Beryllium copper
Contact Plating Material	Gold

Environmental Specifications

Operating Temperature	-40 °C to +65 °C (-40 °F to +149 °F)
Environmental Space	Indoor

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted

