

Fiber Optic Patch Cord, Multi-fiber, Singlemode, 24 fibers, LC/APC to SC/APC, yellow, 26 m

## Product Classification

|                              |                                   |
|------------------------------|-----------------------------------|
| <b>Regional Availability</b> | Latin America   North America     |
| <b>Product Type</b>          | Fiber distribution cable assembly |
| <b>Product Series</b>        | FPM                               |

## General Specifications

|                               |          |
|-------------------------------|----------|
| <b>Color, boot A</b>          | Green    |
| <b>Color, boot B</b>          | Green    |
| <b>Color, connector A</b>     | Green    |
| <b>Color, connector B</b>     | Green    |
| <b>Connector A, quantity</b>  | 24       |
| <b>Connector B, quantity</b>  | 24       |
| <b>Construction Type</b>      | Stranded |
| <b>Interface, Connector A</b> | LC/APC   |
| <b>Interface, Connector B</b> | SC/APC   |
| <b>Jacket Color</b>           | Yellow   |
| <b>Total Fibers, quantity</b> | 24       |

## Dimensions

|                    |                  |
|--------------------|------------------|
| <b>Cord Length</b> | 26 m   85.302 ft |
|--------------------|------------------|

## Optical Specifications

|   |            |
|---|------------|
| <b>Fiber Mode</b>                           | Singlemode |
| <b>Fiber Type</b>                           | OS2        |
| <b>Insertion Loss, maximum, connector A</b> | 0.35 dB    |
| <b>Insertion Loss, maximum, connector B</b> | 0.35 dB    |
| <b>Return Loss, minimum, connector A</b>    | 65 dB      |
| <b>Return Loss, minimum, connector B</b>    | 65 dB      |

## Environmental Specifications

**Environmental Space** Plenum

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

### Agency

### Classification

CHINA-ROHS

Above maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant/Exempted

