



Fiber Optic Patch Cord, OS2, SC/UPC-LC/UPC, 2-fiber RBR, 2.0 mm subunits, 59 m, yellow, 25"/39" breakouts

Product Classification

| | |
|------------------------------|-----------------------------------|
| Regional Availability | Latin America North America |
| Product Type | Fiber distribution cable assembly |
| Product Series | FPM |

General Specifications

| | |
|-------------------------------|----------|
| Connector A, quantity | 2 |
| Color, boot A | Blue |
| Color, connector A | Blue |
| Connector B, quantity | 2 |
| Color, boot B | Blue |
| Color, connector B | Blue |
| Construction Type | Stranded |
| Interface, Connector A | LC/UPC |
| Interface, Connector B | SC/UPC |
| Jacket Color | Yellow |
| Total Fibers, quantity | 2 |

Dimensions

| | |
|-------------------------------------|------------------|
| Breakout Length, connector A | 635 mm 25 in |
| Breakout Length, connector B | 990.6 mm 39 in |
| Cord Length | 59 m 193.57 ft |

Optical Specifications

| | |
|---|------------|
| Fiber Mode | Singlemode |
| Fiber Type | OS2 |
| Insertion Loss, maximum, connector A | 0.3 dB |
| Insertion Loss, maximum, connector B | 0.2 dB |

Return Loss, minimum, connector A 55 dB

Return Loss, minimum, connector B 55 dB

Environmental Specifications

Environmental Space Plenum

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Above maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |

