

F4S-HMQHMQ-1M-P

RSJ4-50 SureFlex® Jumper with interface types 4.3-10 Push Pull Male and 4.3-10 Push Pull Male 1 meter



- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type	SureFlex® Premium, static PIM
Product Brand	HELIAX® SureFlex®
Product Series	RSJ4-50

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	HMQ Male
Interface, Connector B	HMQ Male
Specification Sheet Revision Level	A

Dimensions

Length	1 m 3.281 ft
Nominal Size	1/2 in

Electrical Specifications

3rd Order IMD Static	-117 dBm
3rd Order IMD Static Test Method	Two +43 dBm carriers
DTF, Connector A	34 dB
DTF, Connector B	34 dB

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.065	30.04
1700–2200 MHz	1.083	27.99
2200–2700 MHz	1.119	25.01

F4S-HMQHMQ-1M-P

Jumper Assembly Sample Label



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

Included Products

- RSJ4-50 — RSJ4-50, HELIAX[®] Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket