DFJ-2M4-7-HW-1M

HELIAX® Discrete, 2 multimode fiber, 7 mm LSZH cable. End 1: DLC. End

2: DLC, 1 m

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Wireless Fiber Cable Assemblies

Product Brand HELIAX®

Product Series DFJ

Ordering Note ANDREW® non-standard product

General Specifications

Construction Type Discrete fiber tail

Interface, Connector A DLC

Interface Body Style, connector A Straight

Interface, Connector B DLC

Interface Body Style, connector B Straight

Jacket Color Black

Total Fibers, quantity

Dimensions

Cord Length 1 m | 3.281 ft

Diameter Over Jacket 7 mm | 0.276 in

Material Specifications

Jacket Material Low Smoke Zero Halogen (LSZH)

Optical Specifications

Fiber Mode Multimode

Fiber Type OM4, bend insensitive

Insertion Loss, typical note Insertion loss is measured at 850 nm

Insertion Loss, typical 0.5



DFJ-2M4-7-HW-1M

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +80 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +176 \,^{\circ}\text{F})$

Environmental Space Low Smoke Zero Halogen (LSZH)

Packaging and Weights

Cable weight 25 kg/km | 16.799 lb/kft

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes

Insertion Loss, typical note Insertion loss is measured at a room temp of +20°C (+68°F)

