

F1-XMHR-34N5-TMB

FSJ1-50A SureFlex® Jumper with interface types Nex10 Male and 4.3-10 Male Right angle, 34.5 inches



- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type	Wireless transmission cable assembly
Product Series	FSJ1-50A

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Right angle
Interface, Connector A	Nex10 Male
Interface, Connector B	4.3-10 Male
Specification Sheet Revision Level	A

Dimensions

Length	0.876 m 2.874 ft
Nominal Size	1/4 in

Electrical Specifications

3rd Order IMD	-117 dBm
3rd Order IMD Test Method	Two +43 dBm carriers

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698–2700 MHz	1.16	23
3400–3800 MHz	1.29	18
3800–6000 MHz	1.29	18

Jumper Assembly Sample Label

F1-XMHR-34N5-TMB



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition