

F1R-HMHM-2M-E1

FSJ1RK-50B SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Male, 2 m



- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type	Wireless transmission cable assembly
Product Brand	HELIAX® SureFlex®
Product Series	FSJ1RK-50B

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	4.3-10 Male
Interface, Connector B	4.3-10 Male
Specification Sheet Revision Level	A

Dimensions

Length	2 m 6.562 ft
Nominal Size	1/4 in

Electrical Specifications

3rd Order IMD	-116 dBm
3rd Order IMD Test Method	Two +43 dBm carriers

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
680–960 MHz	1.106	25.96
1700–2200 MHz	1.135	23.98
2300–2700 MHz	1.135	23.98

Jumper Assembly Sample Label

F1R-HMHM-2M-E1



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition