

FTL-77Z015M



TracerLight® Fiber Optic Patch Cord, 1.7 mm duplex, singlemode, SC /UPC to SC/UPC, yellow, 15 m

- Offers a quick and accurate method of identifying the termination point of optical patch cords
- Each end of a TracerLight patch cord features a flashing light source allowing technicians to visually trace individual patch cords
- Dramatically minimizes the risk of taking the wrong fiber out of service while improves system turn-up speed and accuracy
- Ideally suited for Central Offices, Data Centers and cross-connect patching

Product Classification

Regional Availability	Latin America North America
Product Type	Fiber patch cord, duplex
Product Brand	TracerLight®
Product Series	FTL

General Specifications

Color, boot A	Blue
Color, boot B	Blue
Color, connector A	Blue
Color, connector B	Blue
Connector A, quantity	2
Connector B, quantity	2
Interface, Connector A	SC/UPC
Interface, Connector B	SC/UPC
Jacket Color	Yellow
Total Fibers, quantity	2

Dimensions

Cord Length	15 m 49.213 ft
Diameter Over Jacket	1.7 mm 0.067 in

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

FTL-77Z015M

Fiber Type	OS1
Insertion Loss, maximum, connector A	0.2 dB
Insertion Loss, maximum, connector B	0.2 dB
Return Loss, minimum, connector A	55 dB
Return Loss, minimum, connector B	55 dB

Environmental Specifications

Environmental Space	Plenum
----------------------------	--------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted

