

L2B-PDFNR-1M5



LDF2-50 SureFlex® Jumper with interface types N Male Right Angle and 7-16 DIN Female, 1.5 m

OBSOLETE

This product was discontinued on: December 1, 2016

Product Classification

Product Type	Wireless transmission cable assembly
Product Brand	HELIAX® SureFlex®
Product Series	LDF2-50

General Specifications

Attachment, Connector A	Field attachment
Body Style, Connector A	Right angle
Body Style, Connector B	Straight
Interface, Connector A	N Male
Interface, Connector B	7-16 DIN Female
Specification Sheet Revision Level	A

Dimensions

Length	1.5 m 4.921 ft
Nominal Size	3/8 in

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.43	15.05

Jumper Assembly Sample Label

L2B-PDFNR-1M5



Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



Included Products

- | | |
|----------|--|
| 35422-23 | - Heat Treated LDF2-50, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket |
| L2TNR-PL | - Type N Male Right Angle Positive Lock for 3/8 in LDF2-50 cable |
| LDF2-50 | - LDF2-50, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 3/8 in, black PE jacket |