

F2A-HMHM-1M-P-SGW



FSJ2-50 SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Male with HELIAX® SureGuard weatherproofing boot 1 m

- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type Wireless transmission cable assembly

Product Series FSJ2-50

General Specifications

Body Style, Connector A Straight

Body Style, Connector B Straight

Interface, Connector A 4.3-10 Male

Interface, Connector B 4.3-10 Male

Specification Sheet Revision Level A

Dimensions

Length 1 m | 3.281 ft

Nominal Size 3/8 in

Electrical Specifications

3rd Order IMD Static -110 dBm

3rd Order IMD Static Test Method Two +43 dBm carriers

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698–960 MHz	1.1	26.45
1700–2200 MHz	1.1	26.45
2200–2700 MHz	1.1	26.45

Jumper Assembly Sample Label

F2A-HMHM-1M-P-SGW



Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Weatherproofing Method HELIAX[®] SureGuard weatherproofing boot

Packaging and Weights

Included Weatherproofing boot