

PTS1P-NMQR-4

PTS1-50-P SureFlex® Jumper with interface types N Male and QMA Male Right angle, 4 ft



Product Classification

Product Type	Cable assembly, plenum
Product Series	PTS1-50-P

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Right angle
Interface, Connector A	N Male
Interface, Connector B	QMA Male
Specification Sheet Revision Level	A

Dimensions

Length	1.219 m 3.999 ft
Nominal Size	1/4 in

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.288	18

Jumper Assembly Sample Label

PTS1P-NMQR-4



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition