


2-2105061-5



Fiber Optic Patch Cord, Duplex, Multimode, LC/UPC to LC/UPC, LSZH & OFNR, aqua, 25 m

Product Classification

| | |
|------------------------------|--|
| Regional Availability | Asia Australia/New Zealand China India Latin America |
| Portfolio | CommScope® |
| Product Type | Fiber patch cord, duplex |
| Product Series | 210 |

General Specifications


| | |
|-------------------------------|--------|
| Connector A, quantity | 2 |
| Color, boot A | Aqua |
| Color, connector A | Beige |
| Connector B, quantity | 2 |
| Color, boot B | Aqua |
| Color, connector B | Beige |
| Interface, Connector A | LC/UPC |
| Interface, Connector B | LC/UPC |
| Jacket Color | Aqua |
| Total Fibers, quantity | 2 |

Dimensions

| | |
|-----------------------------|-------------------|
| Cord Length | 25 m 82.021 ft |
| Diameter Over Jacket | 1.8 mm 0.071 in |

Ordering Tree

2-2105061-5



| Examples of Lengths (meters) | |
|------------------------------|-----------------|
| -5 | 5 meters |
| 1- -0 | 10 meters |
| 1- -5 | 15 meters |
| 7- -5 | 75 meters |
| 8- -0 | 80 meters |
| 9- -y | Specific length |

Optical Specifications

| | |
|--|-----------------|
| Fiber Mode | Multimode |
| Fiber Type | OM4, LazrSPEED® |
| Insertion Loss, maximum, connector A and B | 0.3 dB |
| Insertion Loss, ULL, maximum, connector A and B | 0.15 dB |

Environmental Specifications

| | |
|--------------------------------|---|
| Environmental Space | Dual Rated LSZH/Riser |
| Qualification Standards | IEC 60332-1 IEC 60332-3 IEC 60754 IEC 61034 |

Packaging and Weights

| | |
|---------------------------|---|
| Packaging quantity | 1 |
|---------------------------|---|

Regulatory Compliance/Certifications

| Agency | Classification |
|------------|---|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |



* Footnotes

Insertion Loss, maximum, connector A and B Insertion loss is measured at a room temp of +20°C (+68°F)