F1R-HMDR-12M-P

FSJ1RK-50B SureFlex® Jumper with interface types 4.3-10 Male and 7-16 DIN Male Right Angle, 12M



WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type SureFlex® Premium, static PIM

Product Brand HELIAX® | SureFlex®

Product Series FSJ1-50B

General Specifications

Body Style, Connector AStraightBody Style, Connector BRight angleInterface, Connector A4.3-10 MaleInterface, Connector B7-16 DIN Male

Specification Sheet Revision Level A

Dimensions

Length 12 m | 39.37 ft

Nominal Size 1/4 in

Electrical Specifications

3rd Order IMD Static -107 dBm

3rd Order IMD Static Test Method Two +43 dBm carriers

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698-960 MHz	1.152	23.02
1700-2200 MHz	1.152	23.02
2500-2700 MHz	1.152	23.02



F1R-HMDR-12M-P

Jumper Assembly Sample Label



Environmental Specifications

EN50575 CPR Cable EuroClass Fire PerformanceB2caEN50575 CPR Cable EuroClass Smoke Ratings1aEN50575 CPR Cable EuroClass Droplets Ratingd0EN50575 CPR Cable EuroClass Acidity Ratinga1

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition