

760161380 | 360-imV-CNTRLR



SYSTIMAX 360™ imVision® Controller

OBSOLETE

This product was discontinued on: January 31, 2019

Replaced By:

760237876
imV-CNTRL-X

imVision Controller X

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio

SYSTIMAX®

Product Type

Controller unit

Product Brand

iPatch® | imVision®

General Specifications

Color

Cool gray

Dimensions

Height

81.28 mm | 3.2 in

Width

19 mm | 0.748 in

Depth

211.33 mm | 8.32 in

Electrical Specifications

Input Voltage

100–240 Vac

Output Current at Voltage, continuous

1.25 A @ 12 Vdc

Power Frequency

50–60 Hz

Material Specifications

760161380 | 360-imV-CNTRLR

Material Type Acrylonitrile butadiene styrene (ABS) | Polycarbonate | Steel

Environmental Specifications

Operating Temperature 0 °C to +50 °C (+32 °F to +122 °F)
Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity Up to 95%, non-condensing
Flammability Rating UL 94 V-0
Safety Standard C-tick | CE | GOST | KC | cUL

Packaging and Weights

Included 16 in panel bus jumper | 7 ft patch cord | Forty-four position bus panel | Power supply, 1.25A @ 12 Vdc output, 100-240 Vac 50-60 Hz input
Packaging quantity 1
Weight, net 1.288 kg | 2.84 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted

