


FPCF-SPSC-S-7M



Fiber Optic Patch Cord, 1.7 mm simplex, standard singlemode, SC/UPC-SC/UPC, 7 m, yellow

Product Classification

| | |
|------------------------------|-------------------------------|
| Regional Availability | Latin America North America |
| Product Type | Fiber patch cord, simplex |
| Product Series | FPCF |

General Specifications

| | |
|-------------------------------|--------|
| Connector A, quantity | 1 |
| Color, boot A | Blue |
| Color, connector A | Blue |
| Connector B, quantity | 1 |
| Color, boot B | Blue |
| Color, connector B | Blue |
| Interface, Connector A | SC/UPC |
| Interface, Connector B | SC/UPC |
| Jacket Color | Yellow |
| Total Fibers, quantity | 1 |

Dimensions

| | |
|-----------------------------|-------------------|
| Cord Length | 7 m 22.966 ft |
| Diameter Over Jacket | 1.7 mm 0.067 in |

Optical Specifications

| | |
|---|------------|
| Fiber Mode | Singlemode |
| Fiber Type | OS1 |
| Insertion Loss, maximum, connector A | 0.2 dB |
| Insertion Loss, maximum, connector B | 0.2 dB |
| Return Loss, minimum, connector A | 55 dB |
| Return Loss, minimum, connector B | 55 dB |

FPCF-SPSC-S-7M

Environmental Specifications

Environmental Space Plenum

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Above maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant |

